

SILTEC

CLEAR RENOV

RENOVATION OF CAR HEADLIGHTS

THE PROFESSIONAL RANGE

DESCRIPTION

CLEAR RENOV contains a specific additive which makes it possible to eliminate micro-scratches on some plastics (renovation of car headlights in polycarbonate), thus restoring brilliance and shine. **CLEAR RENOV** is more than 90% biodegradable in accordance with current legislation.

COMPOSITION

Non-ionic surfactants 0 to 5%.

INSTRUCTIONS FOR USE

Using the sponge provided for that purpose, apply **CLEAR RENOV** cream onto the headlight in a circular movement.
Rub with the rough surface on the soiled areas. Apply on the rest of the headlight with the soft surface.
Rinse with a dampened microfiber cloth.
Repeat the operation if necessary.

PRECAUTIONS FOR USE AND STORAGE

Store in its original packaging in a cool and ventilated area, away from frost and at a temperature always lower than 30°C. Close the packaging tightly after each use. Avoid contact with skin or eyes.
For a professional use.

PACKAGING

500 ml bucket



www.siltec-actalys.com

ACTALYS - ZA DU HAUT DES TAPPES - BP 70065 - 54310 HOMECOURT - FRANCE
TEL +33 3 82 20 67 50 - FAX +33 9 70 61 29 66 - siltec-actalys@orange.fr